

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product form : Mixture
Product name : Pure Goop

1.2. Relevant identified uses of the substance or mixture and uses advised against**1.2.1. Relevant identified uses**

Industrial/Professional use spec : Industrial
For professional use only

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Swagelok
29495 F.A. Lennon Drive
44139 Solon, OH - United States
T 440-349-5600 - F 440-519-3304
www.swagelok.com

1.4. Emergency telephone number

Emergency number : Chemtrec: 800-424-9300

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture**

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labeling according to Regulation (EC) No. 1272/2008 [CLP]

No labeling applicable

2.3. Other hazards

No additional information available

SECTION 3: Composition/Information on ingredients**3.1. Substances**

Not applicable

3.2. Mixtures

This mixture does not contain any substances to be mentioned according to the criteria of section 3.2 of REACH annex II

SECTION 4: First aid measures**4.1. Description of first aid measures**

First-aid measures general : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation : Allow victim to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact : Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact : Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No additional information available

Pure Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.

Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Fire hazard : Not flammable.

Explosion hazard : Product is not explosive.

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire-fighting water from entering environment.

Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

Other information : May decompose at temperatures above 500F/260C to produce organo-chlorine compounds, organo-fluorine compounds, hydrogen fluoride, and chlorine gas.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Do not touch spilled material. Keep upwind. Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with skin and eyes. Do not eat, drink or smoke when using this product. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapor. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood.

Hygiene measures : Always wash hands after handling the product. Do not eat, drink or smoke when using this product. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.

Incompatible products : Strong bases. Strong acids.

Incompatible materials : Sources of ignition. Direct sunlight.

Storage temperature : < 260 °C

Storage area : Store in a well-ventilated place.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Silica, amorphous (7631-86-9)

USA - NIOSH	NIOSH REL (TWA) (mg/m ³)	6 mg/m ³
-------------	--------------------------------------	---------------------

Pure Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station. Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure.

Personal protective equipment:

Avoid all unnecessary exposure.

Materials for protective clothing:

Impervious clothing. Footwear (shoes, boots)

Hand protection:

Protective gloves. Wear protective gloves

Eye protection:

Chemical goggles or safety glasses

Respiratory protection:

Wear appropriate mask

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Paste
Color	: White
Odor	: Neutral
Odor threshold	: No data available
pH	: No data available
Relative evaporation rate (butyl acetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable
Vapor pressure	: No data available
Relative vapor density at 20 °C	: No data available
Relative density	: 2.1 water = 1
Specific gravity / density	: 2.1 g/cm ³
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available
Explosion limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Stable under normal conditions.

10.2. Chemical stability

Stable under normal conditions. Not established.

Pure Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

10.3. Possibility of hazardous reactions

None under normal use. Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Sodium, potassium, barium, calcium, finely divided zinc, aluminum, magnesium, and beryllium. Avoid aluminum threaded connections where galling and seizure may initiate a reaction. Reacts with amines, liquid fluorine, and liquid chlorine trifluoride. Strong acids. Strong bases.

10.6. Hazardous decomposition products

May decompose at temperatures above 500F/260C to produce organo-chlorine compounds, organo-fluorine compounds, hydrogen fluoride, and chlorine gas. fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

Chlorotrifluoroethylene polymer (9002-83-9)

LD50 oral rat	> 9200 mg/kg
---------------	--------------

Silica, amorphous (7631-86-9)

LD50 oral rat	> 5000 mg/kg
LD50 dermal rabbit	> 2000 mg/kg
LC50 inhalation rat (mg/l)	> 2.2 mg/l (Exposure time: 1 h)

Skin corrosion/irritation : Not classified
Serious eye damage/irritation : Not classified
Respiratory or skin sensitization : Not classified
Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified
Reproductive toxicity : Not classified

Specific target organ toxicity – single exposure : Not classified

Specific target organ toxicity – repeated exposure : Not classified

Aspiration hazard : Not classified

Potential Adverse human health effects and symptoms : Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Aquatic acute : Not classified
Aquatic chronic : Not classified

Silica, amorphous (7631-86-9)

LC50 fish 1	5000 mg/l (Exposure time: 96 h - Species: Brachydanio rerio [static])
EC50 Daphnia 1	7600 mg/l (Exposure time: 48 h - Species: Ceriodaphnia dubia)
EC50 72h algae [mg/l] 1	440 mg/l (Species: Pseudokirchneriella subcapitata)

12.2. Persistence and degradability

Pure Goop

Persistence and degradability	Not established.
-------------------------------	------------------

Polytetrafluoroethylene (9002-84-0)

Persistence and degradability	Not established.
-------------------------------	------------------

Silica, amorphous (7631-86-9)

Persistence and degradability	Not established.
-------------------------------	------------------

12.3. Bioaccumulative potential

Pure Goop

Bioaccumulative potential	Not established.
---------------------------	------------------

Pure Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Polytetrafluoroethylene (9002-84-0)	
Bioaccumulative potential	Not established.
Silica, amorphous (7631-86-9)	
BCF fish 1	(no bioaccumulation expected)
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to meet all regulations.
Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

UN-No. (ADR) : Not applicable
UN-No. (IMDG) : Not regulated
UN-No. (IATA) : Not regulated
UN-No. (ADN) : Not applicable
UN-No. (RID) : Not applicable

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable
Proper Shipping Name (IMDG) : Not regulated
Proper Shipping Name (IATA) : Not regulated
Proper Shipping Name (ADN) : Not applicable
Proper Shipping Name (RID) : Not applicable

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not regulated

IATA

Transport hazard class(es) (IATA) : Not regulated

ADN

Transport hazard class(es) (ADN) : Not applicable

RID

Transport hazard class(es) (RID) : Not applicable

14.4. Packing group

Packing group (ADR) : Not applicable
Packing group (IMDG) : Not regulated
Packing group (IATA) : Not regulated
Packing group (ADN) : Not applicable
Packing group (RID) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No

Pure Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Marine pollutant : No
Other information : No supplementary information available

14.6. Special precautions for user

- Overland transport

Not applicable

- Transport by sea

Not regulated

- Air transport

Not regulated

- Inland waterway transport

Not applicable

- Rail transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no REACH candidate substance

Contains no REACH Annex XIV substances.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Other information : None.

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product