

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : VAC Goop

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Industrial/Professional use spec : Industrial
For professional use only
Use of the substance/mixture : Antiseize thread lubricant

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Swagelok
29495 F.A. Lennon Drive
44139 Solon, OH - United States
T 440-349-5600 - F 440-519-3304
www.swagelok.com

1.4. Emergency telephone number

Emergency number : Chemtrec: 800-424-9300

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation Category 2 H315
Serious eye damage/eye irritation Category 2 H319
Specific target organ toxicity (single exposure) Category 3 H335

Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labeling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) : Warning
Hazardous ingredients : Siloxanes and Silicones, methyl 3,3,3-trifluoropropyl
Hazard statements (CLP) : H315 - Causes skin irritation
H319 - Causes serious eye irritation
H335 - May cause respiratory irritation
Precautionary statements (CLP) : P261 - Avoid breathing mist, vapors or spray.
P264 - Wash hands, forearms and face thoroughly after handling.
P271 - Use only outdoors or in a well-ventilated area.
P280 - Wear personal protective equipment.
P302+P352 - IF ON SKIN: Wash with plenty of water.
P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312 - Call a POISON CENTRE or doctor if you feel unwell.
P321 - Specific treatment (see first aid measures on this label)
P332+P313 - If skin irritation occurs: Get medical advice/attention.
P337+P313 - If eye irritation persists: Get medical advice/attention.
P362+P364 - Take off contaminated clothing and wash it before reuse.

VAC Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

P403+P233 - Store in a well-ventilated place. Keep container tightly closed.
P405 - Store locked up.
P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

2.3. Other hazards

No additional information available

SECTION 3: Composition/Information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Siloxanes and Silicones, methyl 3,3,3-trifluoropropyl	(CAS-No.) 63148-56-1 (EC-No.) 613-151-8	80 - 90	Skin Irrit. 2, H315 Eye Irrit. 2, H319 STOT SE 3, H335

Full text of H-phrases: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
First-aid measures after skin contact	: Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention. Specific treatment (see first aid measures on this label).
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation	: May cause respiratory irritation.
Symptoms/effects after skin contact	: Causes skin irritation.
Symptoms/effects after eye contact	: May cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions	: Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire-fighting water from entering environment.
Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures	: May produce carbon monoxide and carbon dioxide. May give off trifluoropropionaldehyde, hydrogen fluoride and perfluorohydrocarbons above 300F.
------------------	--

6.1.1. For non-emergency personnel

Emergency procedures	: Evacuate unnecessary personnel.
----------------------	-----------------------------------

VAC Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapor. Avoid breathing fumes. Use only outdoors or in a well-ventilated area.
Hygiene measures : Wash hands thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : children. Keep container tightly closed.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Personal protective equipment:

Avoid all unnecessary exposure.

Hand protection:

Wear protective gloves.

Eye protection:

Chemical goggles or safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

Wear appropriate mask

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid
Color : Opaque- White.
Odor : Neutral.
Odor threshold : No data available
pH : No data available
Relative evaporation rate (butyl acetate=1) : No data available
Melting point : No data available
Freezing point : No data available
Boiling point : No data available

VAC Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Flash point	: > 250 °F
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable
Vapor pressure	: No data available
Relative vapor density at 20 °C	: No data available
Relative density	: No data available
Specific gravity / density	: 1.45 g/cm ³
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available
Explosion limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

May produce carbon monoxide and carbon dioxide. May give off trifluoropropionaldehyde, hydrogen fluoride and perfluorohydrocarbons above 300F.

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

Hazardous fumes. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Causes skin irritation.
Additional information	: Causes skin irritation
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitization	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity - Description	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity – single exposure	: May cause respiratory irritation.
Additional information	: May cause respiratory irritation
Specific target organ toxicity – repeated exposure	: Not classified
Aspiration hazard	: Not classified
Potential Adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.

VAC Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 12: Ecological information

12.1. Toxicity

Aquatic acute : Not classified
Aquatic chronic : Not classified

12.2. Persistence and degradability

VAC Goop	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

VAC Goop	
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.
Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

UN-No. (ADR) : Not evaluated.
UN-No. (IMDG) : Not evaluated.
UN-No. (IATA) : Not evaluated.
UN-No. (ADN) : Not evaluated.
UN-No. (RID) : Not evaluated.

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not evaluated.
Proper Shipping Name (IMDG) : Not evaluated.
Proper Shipping Name (IATA) : Not evaluated.
Proper Shipping Name (ADN) : Not evaluated.
Proper Shipping Name (RID) : Not evaluated.

Not appl
Not appl
Not appl
Not appl
Not appl

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not evaluated.

IMDG

Transport hazard class(es) (IMDG) : Not evaluated.

IATA

Transport hazard class(es) (IATA) : Not evaluated.

ADN

Transport hazard class(es) (ADN) : Not evaluated.

RID

Transport hazard class(es) (RID) : Not evaluated.

14.4. Packing group

Packing group (ADR) : Not evaluated.

VAC Goop

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Packing group (IMDG) : Not evaluated.
Packing group (IATA) : Not evaluated.
Packing group (ADN) : Not evaluated.
Packing group (RID) : Not evaluated.

14.5. Environmental hazards

Dangerous for the environment : No
Marine pollutant : No
Other information : No supplementary information available

14.6. Special precautions for user

- Overland transport

Not applicable

- Transport by sea

Not applicable

- Air transport

Not applicable

- Inland waterway transport

Not applicable

- Rail transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions
Contains no REACH candidate substance
Contains no REACH Annex XIV substances.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Other information : None.

Full text of H- and EUH-phrases:

Eye Irrit. 2	Serious eye damage/eye irritation Category 2
Skin Irrit. 2	Skin corrosion/irritation Category 2
STOT SE 3	Specific target organ toxicity (single exposure) Category 3
H315	Causes skin irritation
H319	Causes serious eye irritation
H335	May cause respiratory irritation

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product